

Rugmaster 7 & 13 Gallon



Model: MC828333 MC831210 MC829139 MC831470



FOR COMMERCIAL USE ONLY

IMPORTANT SAFETY INSTRUCTIONS

When using an electrical appliance, basic precautions should always be followed, including the following:

READ ALL INSTRUCTIONS BEFORE USING

WARNING - To reduce the risk of fire, electric shock, or injury:

 Do not leave appliance when plugged in. Unplug from outlet when not in use and before servicing.

WARNING

To reduce the risk of electrical shock. Do not expose to rain. Store indoors.

- Do not allow to be used as a toy. Close attention is necessary when used by or near children.
- Use only as described in this manual. Use only manufacturer's recommended attachments.
- Do not use with damaged cord or plug. If appliance is not working as it should, has been dropped, damaged, left outdoors, or dropped into water, return it to a service center.
- Do not pull or carry by cord, use cord as a handle, close a door on cord, or pull cord around sharp edges or corners. Do not run appliance over cord. Keep cord away from heated surfaces.
- Do not unplug by pulling on cord. To unplug, grasp the plug, not the cord.
- Do not handle plug or appliance with wet hands.
- Do not put any object into openings. Do not use with any opening blocked; keep free of dust, lint, hair, and anything that may reduce air flow.
- Keep hair, loose clothing, fingers, and all parts of body away from openings and moving parts.
- Do not pick up anything that is burning or smoking, such as cigarettes, matches, or hot ashes.
- Do not use without dustbag and/or filters in place.
- · Turn off all controls before unplugging.
- Use extra care when cleaning on stairs.
- Do not use to pick up flammable or combustible liquids such as gasoline or use in areas where they may be present.
- Connect to a properly grounded outlet only. See grounding instructions.

SAVE THESE INSTRUCTIONS

INSPECTION

Carefully unpack and inspect your machine for shipping damage. Each unit is tested and thoroughly inspected before shipment, and any damage is the responsibility of the delivery carrier who should be notified immediately.

ELECTRICAL - 115 Volt

This machine is designed to operate on a standard 15 amp. 115 volt, 60 hz, AC circuit. Voltages below 105 volts AC or above 125 volts AC could cause serious damage to the motor.

ELECTRICAL - 240 Volt

This machine is designed to operate on a standard 10 amp. 230 volt, 50 hz, AC circuit.

WARNING


Electric motors can cause explosions when operated near explosive materials or vapors. Do not operate this machine near flammable materials such as solvents, thinners, fuels, grain dust, etc.

GROUNDING INSTRUCTIONS

This appliance must be grounded. If it should malfunction or breakdown, grounding provides a path of least resistance for electric current to reduce the risk of electric shock. This appliance is equipped with a cord having an equipment-grounding conductor and grounding plug. The plug must be plugged into an appropriate outlet that is properly installed and grounded in accordance with all local codes and ordinances.

DANGER


Improper connection of the equipment-grounding conductor can result in a risk of electric shock. Check with a qualified electrician or service person if you are in doubt as to whether the outlet is properly grounded. Do not modify the plug provided with the appliance — if it will not fit the outlet, have a proper outlet installed by a qualified electrician.



OPERATION


Mix the shampoo materials according to the directions on the label. (Extraction Shampoo is mixed 1 ounce per gallon of water.) Add approximately 1/2 gallon of water to the recovery tank with 2 to 3 ounces of Defoamer. (The Defoamer will react faster with the shampoo when diluted with a limited amount of water.) Fit the hose coupling to the wand and the supply tank. If the connection is not complete the shut-off valves inside each connection will not operate and no spray solution will pass through the tubes, as there is a check valve at each connection. As the light weight wand is pulled across the carpet, release the hot shampoo mist. The mist effectively dislodges dirt and residue buildup. The vacuum lifts out embedded dirt and nearly all the moisture for quick drying. Empty the unit using a bucket under the spigot. When empty, proceed with further cleaning. If necessary, clean inside the vacuum to remove all lint, soap, scum, etc. To empty the solution tank, put the hose into the tank.

Vac and Solution Hose Assembly 828924




Parts List

Item	Part #	Qty	Description
1	828062	11	Ties
2	828368	2	Male Quick Coupler
3	828482	1	Solution Hose
4	829111	1	Vac Hose



Care and Maintenance

- 1. Vac motor carbon brushes can be replaced with part number 80940. Worn or damaged carbon brushes can cause overheating and high amperage consumption. A periodic check of these brushes will prevent a more serious problem if worn brushed are continued in use.
- 2. The waste tank should be flushed with clean water after every use taking special care to keep the float age and gate valve area clear of lint and debris.
- 3. Protect the machine from freezing. Subjecting this unit to prolonged periods of sub-freezing temperatures can cause damage to the solution pump and other solution connections. If pump damage does occur, a parts breakdown of the pump can be found on the opposite page.
- 4. This machine is intended for wet pick-up only.
- 5. Storage of the vac and solution hose is not recommended in the waste recover tank. Damage to the standpipe and float can result in this practice.
- 6. Front casters and rear wheels should be lubricated with a light grease or a spray lubrication at least once a month, or more often depending upon the frequency of use. A spray lubrication should also be used on the brass connections periodically.
- 7. Always keep the solution tank screen strainer free of debris, which may get into the tank.
- 8. For best results and longer unit life, we recommend the use of Multi-Clean Extraction Shampoo, Defoamer, and other Multi-Clean carpet care products.



Parts List

1		5	0.4		LIST		04.	Description
2 710203 3 SCR-MC 6-32 x 37 STPL 57 828980 4 Gasket 710378 10 SCR-MC 14-20 x 50 STPL 58 828981 1 Hitting Brass Nipple 1/4 4 SCR-MC 1/4-20 x 1.00 STPL 58 828981 1 Hitting Brass Nipple 1/4 4 SCR-MC 1/4-20 x 1.00 STPL 59 828998 1 H 45 Deg. Elbow 67 712567 2 SCR-MC 1/4-20 x 1.02 STPL 61 150004 1 Strain Relief 7 711227 2 BLT-HH 5/16-18 X .62 62 711400 1 Nut-Pipe Lock 1/2 STR 711257 2 BLT-HH 5/16-18 X .62 62 711400 1 Nut-Pipe Lock 1/2 STR 711257 2 BLT-HH 5/16-18 X .62 62 711400 1 Nut-Pipe Lock 1/2 STR 711257 2 STR 714-20 X 1.02 STR Nip 65 829119 1 Decal Solution Tank 711425 8 Nut-Pianged Wizz 6-32 66 829121 1 Spring Light Handle 7 11435 6 Nut-Pianged Wizz 6-32 66 829121 1 Decal Solution Tank 711435 6 Nut-Pianged Wizz 6-32 66 829121 1 Decal Solution Tank 711435 6 Nut-Pianged Wizz 6-32 66 829121 1 Decal Solution Tank 711435 6 Nut-Pianged Wizz 6-32 66 829121 1 Spring Right Handle 7 11435 6 Nut-Pianged Wizz 6-32 66 829121 1 Spring Right Handle 8 829131 1 Spring Right Handle 8 829131 1 Spring Right Handle 9 Nut-Pianged Wizz 6-32 8 9 82943 2 SS Washer 9 Nut-Pianged Wizz 6-32 8 9 82943 2 SS Washer 9 Nut-Pianged Wizz 6-32 8 9 82943 2 SS Washer 9 Nut-Pianged Wizz 6-32 8 9 82943 2 SS Washer 9 Nut-Pianged Wizz 6-32 8 9 82943 2 SS Washer 9 Nut-Pianged Wizz 6-32 8 9 8 8 9 8 9 8 9 8 9 8 9 8 9 8 9 8 9	Item	Part #	Qty	Description 50 07 04	Item	Part #	Qty	Description
710378 10 SCR-MC 114-20 x 50 STPL 58 828981 1 Fitting Brass Nipple 1/4								
4 1710584 4 SCR-MC 114-20 x 1.00 ST PL 59 328998 1 45 Deg. Elbow 6 710600 2 SCR-MC 114-20 x 1.62 STPL 61 150004 1 Strain Relief 7 711257 2 BLT-HH 516-18 X.62 62 711400 1 Nut-Pipe Lock 1/2 9 711368 4 Nut-Morig 14-20 Nyloc PL 64 829110 1 Spring Left Handle 10 711425 8 Nut-Flanged Wizz 6-32 66 829121 1 Decal Instruction 11 711435 6 Nut-Flanged Wizz 6-32 66 829121 1 Decal Instruction 13 711505 10 WSR-Flat 114 68 829131 1 Spring Ight Handle 15 11 711544 14 WSR-Flat 13 x 1.25 x .05 9 829463 2 SWarber 16 12 171540 14 WSR-Flat 31 x 7.5 x .06 STPL 70 450081 1 Spring Ight Handle 18 <								
6 712667 2 SCR-MC 1/4-20 X 2.00 SS 60 829079 1 Gasket 7 71027 2 SCR-MC 1/4-20 X 1.62 STPL 61 150004 1 Strain Relief 7 711227 2 BLT-HH 57/6-18 X 62 62 711400 1 Nut-Pipe Lock 1/2 8 71368 4 Nut-Wing 1/4-20 ST NI 63 829019 1 Spring Left Handle 10 711425 8 Nut-Flanged Wizz 1/4-20 65 829119 1 Decal Solution Tank 12 711438 3 Nut-Flanged Wizz 1/4-20 66 829119 1 Decal Instruction 12 711438 3 Nut-Flanged Wizz 1/4-20 66 829119 1 Decal Instruction 15 711631 4 WSR-Flat 31 x 1.25 x .05 69 829463 2 SS Washer 15 18 715756 2 WSR-Flat 31 x .75 x .06 STPL 70 450081 1 WSR-SS 1.908 x 2.41 x .03 16 171563 <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td>•</td>								•
6 710800 2 SCR-MC 1/4-20 X 1.62 STPL 61 150004 1 Strain Relief 7 71127 2 BLT-HH 5/16-18 X 62 62 71140 1 Nut-Pipe Lock 1/2 8 711382 4 Nut-Acorn 1/4-20 ST NI 63 829084 1 Hinge 9 711383 4 Nut-Relinged Wizz 1/4-20 65 829119 1 Decal Solution Tank 10 711425 8 Nut-Flanged Wizz 6-32 66 829121 1 Decal Solution Tank 11 711435 6 Nut-Flanged Wizz 6-32 66 829119 1 Decal Solution Tank 12 711436 1 WSR-Flat 1/4 68 829131 1 Spring Left Handle 13 711505 10 WSR-Flat 1/4 68 829131 1 Spring Right Handle 14 711516 4 WSR-Flat 1/4 1 1 SSR-Flat 1/4 1 SSR-Flat 1/4 1 1 SSR-Flat 1/4 1								_
7 711227 2 BLT-HH 5/16-18 X 62 62 711400 1 Nut-Pipe Lock 1/2 Hinge 9 711368 4 Nut-Acom 1/4-20 ST Ni 63 829084 1 Hinge 9 711368 4 Nut-Wing 1/4-20 Nyloc PL 64 829110 1 Spring Left Handle 10 711425 8 Nut-Flanged Wizz 1/4-20 65 829119 1 Decal Solution Tank 171435 6 Nut-Flanged Wizz 1/4-20 66 829119 1 Decal Solution Tank 171435 6 Nut-Hanged Wizz 1/4-20 66 829121 1 Decal Solution Tank 171436 1 Decal Instruction 171436 1 Decal Instruction 171436 1 Nut-Hanged Wizz 1/4-20 66 829121 1 Decal Solution Tank 171515 1 Decal Instruction 1714 1 Nut-Flanged Wizz 1/4-20 66 829131 1 Spring Right Handle 171516 4 WSR-Flat 31 x 1.25 x .05 69 829463 2 SWasher 17157 1 Use Item 17 70 450081 1 WSR-SS 1.908 x 2.41 x .03 SWasher 17157 1 Syming Right Handle 17157 1 Syming Right								
8 711352 4 Nut-Wing 1/4-20 ST NI 63 829084 1 Hinge 10 711368 4 Nut-Wing 1/4-20 Nyloc PL 64 829110 1 Spring Left Handle 10 711425 8 Nut-Flanged Wizz 1/4-20 65 829119 1 Decal Solution Tank 11 711435 6 Nut-Flanged Wizz 6-32 66 829131 1 Decal Instruction 13 711505 10 WSR-Flat 1/4 68 829131 1 Spring Right Handle 15 WSR-Flat 1/4 68 829131 1 Spring Right Handle 16 Use Item 17 70 45081 1 WSR-S 1.90 x 2.41 x .03 16 Use Item 17 70 45081 1 WSR-S 1.90 x 2.41 x .03 17 711544 14 WSR-Flett .31 x .75 x .06 STPL 72 WSR-Flett .31 x .75 x .06 STPL 72 18 711503 12 WSR-Flett .52 x .87 x .06 PL 75 740014 3 Timin Indept Mandle								
9 711368 4 Nut-Flanged Wizz 1/4-20 65 829119 1 Decal Solution Tank 10 711425 8 Nut-Flanged Wizz 1/4-20 65 829119 1 Decal Solution Tank 11 711435 6 Nut-Flanged Wizz 6-32 66 829121 1 Decal Solution Tank 12 711438 3 Nut-Hex 6-32 BR Nipl 67 829130 2 Clip Bumper 13 711505 10 WSR-Flat 1/4 68 829131 1 Spring Right Handle 14 711516 4 WSR-Flat 3/1 x 1.25 x .05 69 829463 2 SWasher 15 Use Item 17 70 450081 1 WSR-SE 1-908 x 2.41 x .03 16 17 17 711544 14 WSR-Helical 1/4 72 18 711575 2 WSR-Flat 1/3 1 x .75 x .06 STPL 73 829851 1 Gate Valve 19 712077 6 SCR-SEMS TH 6-32 x .62 Zinc 74 830064 1 Wire Lead Asm 19 712077 6 SCR-SEMS TH 6-32 x .62 Zinc 75 740014 3 Terminal QC Fem 1/4 Full Ins 11 712310 4 WSR-Flat 1/5 x .87 x .06 PL 76 831257 1 Fitting Brass 90 1/4 MPT 12 71263 1 Nut-Hex 10-24 SS Nyloc 79 831306 1 Salid String			2					
10								
11				,				
12		711425						
13	11	711435	6	Nut-Flanged Wizz 6-32				
Table Tabl	12	711438	3	Nut-Hex 6-32 BR Nipl				·
Use Item 17	13	711505	10	WSR-Flat 1/4	68	829131		Spring Right Handle
16	14	711516	4	WSR-Flat .31 x 1.25 x .05	69	829463	2	SS Washer
17	15			Use Item 17	70	450081	1	WSR-SS 1.908 x 2.41 x .03
18	16			Use Item 17	71	829651	1	Gate Valve
19	17	711544	14	WSR-Helical 1/4	72			
19	18	711575	2	WSR-Flat .31 x .75 x .06 STPL	73	829851	1	Flgd. Twst. Loc FM Midget
20 711503 12 WSR-Flatt #10 75 740014 3 Terminal QC Fem 1/4 Full Ins 21 712310 4 WSR-Flatt .52 x .87 x .06 PL "76 831257 1 Wire Lead Asm Black 21 712764 2 WSR SS #10 77 831330 1 Fitting Brass 90 1/4 MPT 23 710182 3 SCR 1/4-20 x 1.00 STPL 78 831338 1 Float Frame 24 712638 1 Nut-Hex 10-24 SS Nyloc 79 831344 1 Ball 25 712760 3 WSR-Flatt .56 x 1.06 x .04 SS *80 831657 3 Clip 26 712810 2 SCR-MC 10-24 x .37 STPL 81 831812 2 Fitting Abs 1.5MPT 1.5 Hose 27 712533 1 SCR-MC 10-24 x .37 STPL 81 831812 2 Fitting Abs 1.5MPT 1.5 Hose 28 712904 2 Nut-Acorn 10-24 BR Nipl *83 740033 1 Terminal QL Male 1/4 Full Inc 29 7608		712077			*74	830064	1	Wire Lead Asm
21 712310 4 WSR-Flat .52 x .87 x .06 PL *76 831257 1 Wire Lead Asm Black 22 712764 2 WSR SS #10 77 831306 1 Fitting Brass 90 1/4 MPT 23 71082 3 SCR 1/4-20 x 1.00 STPL 78 831338 1 Float Frame 24 712638 1 Nut-Hex 10-24 SS Nyloc 79 831344 1 Ball 25 71260 3 WSR-Flat .56 x 1.06 x .04 SS 80 831657 3 Clp 26 712810 2 SCR-MC 10-24 x 37 STPL 81 831812 2 Fitting Abs 1.5MPT 1.5 Hose 27 712533 1 SCR-MC 10-24 x 1.25 SS 82 Use Item 18 & 11 Terminal QC Male 1/4 Full Inc 28 712904 2 Nut-Acorn 10-24 BR Nipl 83 740033 1 Terminal QC Male 1/4 Full Inc 31 270249 1 Hose Clamp #24 86 833045 1 Base Plate Weldment 31 270249 1 <td></td> <td></td> <td></td> <td></td> <td>75</td> <td>740014</td> <td>3</td> <td>Terminal QC Fem 1/4 Full Ins</td>					75	740014	3	Terminal QC Fem 1/4 Full Ins
22 712764 2 WSR SS #10 77 831308 1 Fitting Brass 90 1/4 MPT 23 710182 3 SCR 1/4-20 x 1.00 STPL 78 831338 1 Float Frame 24 712638 1 Nut-Hav 10-24 SS Nyloc 79 831344 1 Ball 25 712760 3 WSR-Flat .56 x 1.06 x .04 SS *80 831657 3 Clip 26 712810 2 SCR-MC 10-24 x .37 STPL 81 831812 2 Fitting Abs 1.5MPT 1.5 Hose Use Item 18 & 11 28 712904 2 Nut-Acorn 10-24 BR Nipl *83 740033 1 Terminal QC Male 1/4 Full Inc Use Item 18 & 11 29 760859 1 Clamp, Hose 84 8330045 1 Base Plate Weldment 31 270249 1 Hose Clamp #24 86 833064 1 Hose Assy25 x 20" 32 809754 2 Switch Rocker 87 833150 1 Adapter Abs 1.5FPT a 1.5 Slip 34 8288								
Time							1	
24 712338 1 Nut-Hex 10-24 SS Nyloc 79 831344 1 Ball 25 712760 3 WSR-Flat .56 x 1.06 x .04 SS *80 831657 3 Clip 26 712810 2 SCR-MC 10-24 x .37 STPL 81 831812 2 Fitting Abs 1.5MPT 1.5 Hose 27 712533 1 SCR-MC 10-24 x .37 STPL 81 831812 2 Fitting Abs 1.5MPT 1.5 Hose 28 712904 2 Nut-Acorn 10-24 BR Nipl *83 740033 1 Terminal QC Male 1/4 Full Inc 29 760859 1 Clamp, Hose 84 833039 1 Louver 30 740010 1 Ring Terminal #10 85 833045 1 Base Plate Weldment 31 270249 1 Hose Clamp #24 86 833064 1 Hose Assy25 x 20" 32 809754 2 Switch Rocker 87 833150 1 Adapter Abs 1.5FPT a 1.5 Slip 42 828913 1								•
25 712760 3 WSR-Flat .56 x 1.06 x .04 SS *80 831657 3 Clip 26 712810 2 SCR-MC 10-24 x .37 STPL 81 831812 2 Fitting Abs 1.5MPT 1.5 Hose 27 712533 1 SCR-MC 10-24 x 1.25 SS 82 Use Item 18 & 11 Use Item 18 & 11 Terminal QC Male 1/4 Full Inc 29 760859 1 Clamp, Hose 84 833039 1 Louver Louver 30 740010 1 Ring Terminal #10 85 833045 1 Base Plate Weldment 31 270249 1 Hose Clamp #24 86 833064 1 Hose Assy25 x 20" 32 809754 2 Switch Rocker 87 833159 1 Elbow 90 Deg. 1.5 x 1 33 828970 1 BIP2-60 Female Coupler 88 833160 1 Adapter Abs 1.5FPT a 1.5 Slip 34 8288913 1 Latch Handle RH 90 833460 1 Hose Assy25 x 22.5" 36 828917 1 Brace Handle RH 91 833878								
26 712810 2 SCR-MC 10-24 x .37 STPL 81 831812 2 Fitting Abs 1.5MPT 1.5 Hose Use Item 18 & 11 27 712533 1 SCR-MC 10-24 x 1.25 SS 82 Use Item 18 & 11 28 712904 2 Nut-Acorn 10-24 BR Nipl *83 740033 1 Terminal QC Male 1/4 Full Inc 29 760859 1 Clamp, Hose 84 833039 1 Louver 30 740010 1 Ring Terminal #10 85 833045 1 Base Plate Weldment 31 270249 1 Hose Clamp #24 86 833064 1 Hose Assy25 x 20" 32 809754 2 Switch Rocker 87 833159 1 Elbow 90 Deg. 1.5 x 1 3 33 828973 1 BH2-60 Female Coupler 88 833460 1 Adapter Abs 1.5FPT a 1.5 Slip 34 828933 8 Rivet Pop *89 833459 1 Wire Lead Assembly White 35 828911 1								
27 712533 1 SCR-MC 10-24 x 1.25 SS 82 Use Item 18 & 11 28 712904 2 Nut-Acorn 10-24 BR Nipl *83 740033 1 Terminal QC Male 1/4 Full Inc 29 760859 1 Clamp, Hose 84 833039 1 Louver 30 740010 1 Ring Terminal #10 85 833045 1 Base Plate Weldment 31 270249 1 Hose Clamp #24 86 833064 1 Hose Assy25 x 20" 32 809754 2 Switch Rocker 87 833159 1 Elbow 90 Deg .1.5 x 1 1 33 828370 1 BH2-60 Female Coupler 88 833160 1 Adapter Abs 1.5FPT a 1.5 Slip 34 8288913 1 Latch Handle RH 90 833460 1 Hose Assy25 x 22.5" 36 828914 1 Latch Handle LH 91 833878 1 1.5 Hose Assy. 37 828917 1 Brace Handle LH								•
28 712904 2 Nut-Acorn 10-24 BR Nipl *83 740033 1 Terminal QC Male 1/4 Full Inc 29 760859 1 Clamp, Hose 84 833039 1 Louver 30 740010 1 Ring Terminal #10 85 833045 1 Base Plate Weldment 31 270249 1 Hose Clamp #24 86 833064 1 Hose Assy25 x 20" 32 809754 2 Switch Rocker 87 833159 1 Elbow 90 Deg. 1.5 x 1 1 33 828370 1 BH2-60 Female Coupler 88 833160 1 Adapter Abs 1.5FPT a 1.5 Slip 34 8288913 1 Latch Handle RH 90 833460 1 Hose Assy25 x 22.5" 36 828914 1 Latch Handle RH 91 833878 1 1.5 Hose Assy25 x 22.5" 37 828917 1 Brace Handle RH 92 715385 2 Decal, "Minuteman" Lt Grey 38 828918						001012	_	_
29 760859 1 Clamp, Hose 84 833039 1 Louver 30 740010 1 Ring Terminal #10 85 833045 1 Base Plate Weldment 31 270249 1 Hose Clamp #24 86 833064 1 Hose Assy25 x 20" 32 809754 2 Switch Rocker 87 833159 1 Elbow 90 Deg. 1.5 x 1 33 828370 1 BH2-60 Female Coupler 88 833160 1 Adapter Abs 1.5FPT a 1.5 Slip 34 828913 1 Latch Handle RH 90 833460 1 Hose Assy. 25 x 22.5" 36 828914 1 Latch Handle RH 91 833878 1 1.5 Hose Assy. 37 828917 1 Brace Handle LH 91 833878 1 1.5 Hose Assy. 38 828918 1 Brace Handle LH 93 715029 1 Decal, Serial Name Plate 39 828921 1 Handle *94						740033	1	
30 740010 1 Ring Terminal #10 85 833045 1 Base Plate Weldment 31 270249 1 Hose Clamp #24 86 833064 1 Hose Assy25 x 20" 32 809754 2 Switch Rocker 87 833159 1 Elbow 90 Deg. 1.5 x 1 33 828370 1 BH2-60 Female Coupler 88 833160 1 Adapter Abs 1.5FPT a 1.5 Slip 34 828893 8 Rivet Pop *89 833459 1 Wire Lead Assembly White 35 828913 1 Latch Handle RH 90 833460 1 Hose Assy25 x 22.5" 36 828914 1 Latch Handle LH 91 833878 1 1.5 Hose Assy. 37 828917 1 Brace Handle RH 92 715385 2 Decal, Serial Name Plate 38 828918 1 Vac & Solution Hose Assy. 95 829881 1 Cord 14/3 x 30 FT. 41 828933 2				-				
31 270249 1 Hose Clamp #24 86 833064 1 Hose Assy25 x 20" 32 809754 2 Switch Rocker 87 833159 1 Elbow 90 Deg. 1.5 x 1 33 828370 1 BH2-60 Female Coupler 88 833160 1 Adapter Abs 1.5FPT a 1.5 Slip 34 828893 8 Rivet Pop *89 833459 1 Wire Lead Assembly White 35 828913 1 Latch Handle RH 90 833460 1 Hose Assy25 x 22.5" 36 828914 1 Latch Handle LH 91 833878 1 1.5 Hose Assy. 37 828917 1 Brace Handle LH 92 715385 2 Decal, "Minuteman" Lt Grey 38 828918 1 Brace Handle LH 93 715029 1 Decal, Serial Name Plate 40 828924 1 Vac & Solution Hose Assy. 95 829881 1 Cord 14/3 x 30 FT. 41 828933 2								
32 809754 2 Switch Rocker 87 833159 1 Elbow 90 Deg. 1.5 x 1 33 828370 1 BH2-60 Female Coupler 88 833160 1 Adapter Abs 1.5FPT a 1.5 Slip 34 828893 8 Rivet Pop *89 833459 1 Wire Lead Assembly White 35 828913 1 Latch Handle RH 90 833460 1 Hose Assy25 x 22.5" 36 828914 1 Latch Handle LH 91 833878 1 1.5 Hose Assy. 37 828917 1 Brace Handle RH 92 715385 2 Decal, "Minuteman" Lt Grey 38 828918 1 Brace Handle LH 93 715029 1 Decal, Serial Name Plate 39 828921 1 Handle *94 740025 1 Term, FM 1/4 12-10 INS 40 828934 2 Spacer 97 43 828935 2 Spacer 97 43 828936 <td></td> <td></td> <td></td> <td>•</td> <td></td> <td></td> <td></td> <td></td>				•				
33 828370 1 BH2-60 Female Coupler 88 833160 1 Adapter Abs 1.5FPT a 1.5 Slip 34 828893 8 Rivet Pop *89 833459 1 Wire Lead Assembly White 35 828913 1 Latch Handle RH 90 833460 1 Hose Assy25 x 22.5" 36 828914 1 Latch Handle LH 91 833878 1 1.5 Hose Assy25 x 22.5" 37 828917 1 Brace Handle RH 92 715385 2 Decal, "Minuteman" Lt Grey 38 828918 1 Brace Handle LH 93 715029 1 Decal, Serial Name Plate 39 828921 1 Handle *94 740025 1 Term, FM 1/4 12-10 INS *40 828924 1 Vac & Solution Hose Assy. 95 829881 1 Cord 14/3 x 30 FT. 41 828933 2 Wheel *96 830294 1 Lead Black 42 828934 2 Spacer 97 43 828935 2 Spacer 98 </td <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>								
34 828893 8 Rivet Pop *89 833459 1 Wire Lead Assembly White 35 828913 1 Latch Handle RH 90 833460 1 Hose Assy25 x 22.5" 36 828914 1 Latch Handle LH 91 833878 1 1.5 Hose Assy. 37 828917 1 Brace Handle RH 92 715385 2 Decal, "Minuteman" Lt Grey 38 828918 1 Brace Handle LH 93 715029 1 Decal, Serial Name Plate 39 828921 1 Handle *94 740025 1 Term, FM 1/4 12-10 INS *40 828933 2 Wheel *96 830294 1 Lead Black *42 828934 2 Spacer 97 *43 828935 2 Spacer 98 809444 2 Clip Cord *44 828936 2 Caster 2 1/2 PLT MT 99 833138 1 Tank SNV 13 Gal. *45 828942 4 Support Bracket 99A 833138 1 <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>								
35 828913 1 Latch Handle RH 90 833460 1 Hose Assy25 x 22.5" 36 828914 1 Latch Handle LH 91 833878 1 1.5 Hose Assy. 37 828917 1 Brace Handle RH 92 715385 2 Decal, "Minuteman" Lt Grey 38 828918 1 Brace Handle LH 93 715029 1 Decal, Serial Name Plate 39 828921 1 Handle *94 740025 1 Term, FM 1/4 12-10 INS *40 828924 1 Vac & Solution Hose Assy. 95 829881 1 Cord 14/3 x 30 FT. 41 828933 2 Wheel *96 830294 1 Lead Black 42 828934 2 Spacer 97 43 828935 2 Spacer 98 809444 2 Clip Cord 44 828936 2 Caster 2 1/2 PLT MT 99 833138 1 Tank SNV 13 Gal.								·
36 828914 1 Latch Handle LH 91 833878 1 1.5 Hose Assy. 37 828917 1 Brace Handle RH 92 715385 2 Decal, "Minuteman" Lt Grey 38 828918 1 Brace Handle LH 93 715029 1 Decal, Serial Name Plate 39 828921 1 Handle *94 740025 1 Term, FM 1/4 12-10 INS *40 828924 1 Vac & Solution Hose Assy. 95 829881 1 Cord 14/3 x 30 FT. 41 828933 2 Wheel *96 830294 1 Lead Black 42 828934 2 Spacer 97 43 828935 2 Spacer 98 809444 2 Clip Cord 44 828936 2 Caster 2 1/2 PLT MT 99 833138 1 Tank SNV 13 Gal. 45 828942 4 Support Bracket 99A 833138 1 Tank SNV 7 Gal. 46 828943 2 Axle Weldment 100 833066 1								
37 828917 1 Brace Handle RH 92 715385 2 Decal, "Minuteman" Lt Grey 38 828918 1 Brace Handle LH 93 715029 1 Decal, Serial Name Plate 39 828921 1 Handle *94 740025 1 Term, FM 1/4 12-10 INS *40 828924 1 Vac & Solution Hose Assy. 95 829881 1 Cord 14/3 x 30 FT. 41 828933 2 Wheel *96 830294 1 Lead Black 42 828934 2 Spacer 97 43 828935 2 Spacer 98 809444 2 Clip Cord 44 828936 2 Caster 2 1/2 PLT MT 99 833138 1 Tank SNV 7 Gal. 45 828942 4 Support Bracket 99A 833138 1 Tank SNV 7 Gal. 46 828943 2 Axle Weldment 100 833066 1 Vac Motor Mtg. 47 828945 1 Bulkhead Fitting 1/4 x 3/4 101 833067 <								
38 828918 1 Brace Handle LH 93 715029 1 Decal, Serial Name Plate 39 828921 1 Handle *94 740025 1 Term, FM 1/4 12-10 INS *40 828924 1 Vac & Solution Hose Assy. 95 829881 1 Cord 14/3 x 30 FT. 41 828933 2 Wheel *96 830294 1 Lead Black 42 828934 2 Spacer 97 43 828935 2 Spacer 98 809444 2 Clip Cord 44 828936 2 Caster 2 1/2 PLT MT 99 833138 1 Tank SNV 13 Gal. 45 828942 4 Support Bracket 99A 833138 1 Tank SNV 7 Gal. 46 828943 2 Axle Weldment 100 833056 1 Vac Motor Mtg. 47 828945 1 Bulkhead Fitting 1/4 x 3/4 101 833066 1 Pump 100 PSI 115V								•
39 828921 1 Handle *94 740025 1 Term, FM 1/4 12-10 INS *40 828924 1 Vac & Solution Hose Assy. 95 829881 1 Cord 14/3 x 30 FT. 41 828933 2 Wheel *96 830294 1 Lead Black 42 828934 2 Spacer 97 43 828935 2 Spacer 98 809444 2 Clip Cord 44 828936 2 Caster 2 1/2 PLT MT 99 833047 1 Tank SNV 13 Gal. 45 828942 4 Support Bracket 99A 833138 1 Tank SNV 7 Gal. 46 828943 2 Axle Weldment 100 833056 1 Vac Motor Mtg. 47 828945 1 Bulkhead Fitting 1/4 x 3/4 101 833067 1 Pump 100 PSI 115V 48 828959 1 Plastic Elbow 1-1/2 101A 833068 1 Pump 100 PSI 240V 49 828970 3 WSR Neoprene 1.81 x 2.4 x .125 102A 833148 1 <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>								
*40 828924 1 Vac & Solution Hose Assy. 95 829881 1 Cord 14/3 x 30 FT. 41 828933 2 Wheel *96 830294 1 Lead Black 42 828934 2 Spacer 97 43 828935 2 Spacer 98 809444 2 Clip Cord 44 828936 2 Caster 2 1/2 PLT MT 99 833047 1 Tank SNV 13 Gal. 45 828942 4 Support Bracket 99A 833138 1 Tank SNV 7 Gal. 46 828943 2 Axle Weldment 100 833056 1 Vac Motor Mtg. 47 828945 1 Bulkhead Fitting 1/4 x 3/4 101 833067 1 Pump 100 PSI 115V 48 828959 1 Plastic Elbow 1-1/2 101A 833068 1 Pump 100 PSI 240V 49 828961 1 Cover 102 833147 1 Vac Mtr 120V 50 828970 3 WSR Neoprene 1.81 x 2.4 x .125 102A 833148 1 Vac Mtr 240V 51 828971 1 Nut 1-1/2 Pipe Thread 103 833164 1 Pipe 1.5 x 12 (13 gal) 52 828972 1 Gasket 103A 833137 1 Pipe 1.5 x 6 (7 gal) 53 828974 1 Strainer 104 833463 1 Lead White 54 828975 2 WSR Neoprene .75 x 1.5 x .09 105 833607 1 Decal 55 808077 1 Bumper 10" *106 833826 1 Lint Bag								
41 828933 2 Wheel *96 830294 1 Lead Black 42 828934 2 Spacer 97 43 828935 2 Spacer 98 809444 2 Clip Cord 44 828936 2 Caster 2 1/2 PLT MT 99 833047 1 Tank SNV 13 Gal. 45 828942 4 Support Bracket 99A 833138 1 Tank SNV 7 Gal. 46 828943 2 Axle Weldment 100 833056 1 Vac Motor Mtg. 47 828945 1 Bulkhead Fitting 1/4 x 3/4 101 833067 1 Pump 100 PSI 115V 48 828959 1 Plastic Elbow 1-1/2 101A 833068 1 Pump 100 PSI 240V 49 828961 1 Cover 102 833147 1 Vac Mtr 120V 50 828970 3 WSR Neoprene 1.81 x 2.4 x .125 102A 833148 1 Vac Mtr 240V 51 828971 1 Nut 1-1/2 Pipe Thread 103 833137 1								
42 828934 2 Spacer 97 43 828935 2 Spacer 98 809444 2 Clip Cord 44 828936 2 Caster 2 1/2 PLT MT 99 833047 1 Tank SNV 13 Gal. 45 828942 4 Support Bracket 99A 833138 1 Tank SNV 7 Gal. 46 828943 2 Axle Weldment 100 833056 1 Vac Motor Mtg. 47 828945 1 Bulkhead Fitting 1/4 x 3/4 101 833067 1 Pump 100 PSI 115V 48 828959 1 Plastic Elbow 1-1/2 101A 833068 1 Pump 100 PSI 240V 49 828961 1 Cover 102 833147 1 Vac Mtr 120V 50 828970 3 WSR Neoprene 1.81 x 2.4 x .125 102A 833148 1 Vac Mtr 240V 51 828971 1 Nut 1-1/2 Pipe Thread 103 833164 1 Pipe 1.5 x 6 (7 gal) 52 828972 1 Gasket 103A 833463 <t< td=""><td></td><td></td><td></td><td>•</td><td></td><td></td><td></td><td></td></t<>				•				
43 828935 2 Spacer 98 809444 2 Clip Cord 44 828936 2 Caster 2 1/2 PLT MT 99 833047 1 Tank SNV 13 Gal. 45 828942 4 Support Bracket 99A 833138 1 Tank SNV 7 Gal. 46 828943 2 Axle Weldment 100 833056 1 Vac Motor Mtg. 47 828945 1 Bulkhead Fitting 1/4 x 3/4 101 833067 1 Pump 100 PSI 115V 48 828959 1 Plastic Elbow 1-1/2 101A 833068 1 Pump 100 PSI 240V 49 828961 1 Cover 102 833147 1 Vac Mtr 120V 50 828970 3 WSR Neoprene 1.81 x 2.4 x .125 102A 833148 1 Vac Mtr 240V 51 828971 1 Nut 1-1/2 Pipe Thread 103 833137 1 Pipe 1.5 x 6 (7 gal) 52 828974 1 Strainer 104 833463 1 Lead White 54 828975 2						830294	1	Lead Віаск
44 828936 2 Caster 2 1/2 PLT MT 99 833047 1 Tank SNV 13 Gal. 45 828942 4 Support Bracket 99A 833138 1 Tank SNV 7 Gal. 46 828943 2 Axle Weldment 100 833056 1 Vac Motor Mtg. 47 828945 1 Bulkhead Fitting 1/4 x 3/4 101 833067 1 Pump 100 PSI 115V 48 828959 1 Plastic Elbow 1-1/2 101A 833068 1 Pump 100 PSI 240V 49 828961 1 Cover 102 833147 1 Vac Mtr 120V 50 828970 3 WSR Neoprene 1.81 x 2.4 x .125 102A 833148 1 Vac Mtr 240V 51 828971 1 Nut 1-1/2 Pipe Thread 103 833164 1 Pipe 1.5 x 12 (13 gal) 52 828972 1 Gasket 103A 833137 1 Pipe 1.5 x 6 (7 gal) 53 828974 1 Strainer 104 833607 1 Lead White 54 828975				•			_	
45 828942 4 Support Bracket 99A 833138 1 Tank SNV 7 Gal. 46 828943 2 Axle Weldment 100 833056 1 Vac Motor Mtg. 47 828945 1 Bulkhead Fitting 1/4 x 3/4 101 833067 1 Pump 100 PSI 115V 48 828959 1 Plastic Elbow 1-1/2 101A 833068 1 Pump 100 PSI 240V 49 828961 1 Cover 102 833147 1 Vac Mtr 120V 50 828970 3 WSR Neoprene 1.81 x 2.4 x .125 102A 833148 1 Vac Mtr 240V 51 828971 1 Nut 1-1/2 Pipe Thread 103 833164 1 Pipe 1.5 x 12 (13 gal) 52 828972 1 Gasket 103A 833137 1 Pipe 1.5 x 6 (7 gal) 53 828974 1 Strainer 104 833463 1 Lead White 54 828975 2 WSR Neoprene .75 x 1.5 x .09 105 833607 1 Decal 55 808077 <				•				•
46 828943 2 Axle Weldment 100 833056 1 Vac Motor Mtg. 47 828945 1 Bulkhead Fitting 1/4 x 3/4 101 833067 1 Pump 100 PSI 115V 48 828959 1 Plastic Elbow 1-1/2 101A 833068 1 Pump 100 PSI 240V 49 828961 1 Cover 102 833147 1 Vac Mtr 120V 50 828970 3 WSR Neoprene 1.81 x 2.4 x .125 102A 833148 1 Vac Mtr 240V 51 828971 1 Nut 1-1/2 Pipe Thread 103 833164 1 Pipe 1.5 x 12 (13 gal) 52 828972 1 Gasket 103A 833137 1 Pipe 1.5 x 6 (7 gal) 53 828974 1 Strainer 104 833463 1 Lead White 54 828975 2 WSR Neoprene .75 x 1.5 x .09 105 833607 1 Decal 55 808077 1 Bumper 10" *106 833826 1 Lint Bag								
47 828945 1 Bulkhead Fitting 1/4 x 3/4 101 833067 1 Pump 100 PSI 115V 48 828959 1 Plastic Elbow 1-1/2 101A 833068 1 Pump 100 PSI 240V 49 828961 1 Cover 102 833147 1 Vac Mtr 120V 50 828970 3 WSR Neoprene 1.81 x 2.4 x .125 102A 833148 1 Vac Mtr 240V 51 828971 1 Nut 1-1/2 Pipe Thread 103 833164 1 Pipe 1.5 x 12 (13 gal) 52 828972 1 Gasket 103A 833137 1 Pipe 1.5 x 6 (7 gal) 53 828974 1 Strainer 104 833463 1 Lead White 54 828975 2 WSR Neoprene .75 x 1.5 x .09 105 833607 1 Decal 55 808077 1 Bumper 10" *106 833826 1 Lint Bag			4	• •				
48 828959 1 Plastic Elbow 1-1/2 101A 833068 1 Pump 100 PSI 240V 49 828961 1 Cover 102 833147 1 Vac Mtr 120V 50 828970 3 WSR Neoprene 1.81 x 2.4 x .125 102A 833148 1 Vac Mtr 240V 51 828971 1 Nut 1-1/2 Pipe Thread 103 833164 1 Pipe 1.5 x 12 (13 gal) 52 828972 1 Gasket 103A 833137 1 Pipe 1.5 x 6 (7 gal) 53 828974 1 Strainer 104 833463 1 Lead White 54 828975 2 WSR Neoprene .75 x 1.5 x .09 105 833607 1 Decal 55 808077 1 Bumper 10" *106 833826 1 Lint Bag	46		2	Axle Weldment				· ·
49 828961 1 Cover 102 833147 1 Vac Mtr 120V 50 828970 3 WSR Neoprene 1.81 x 2.4 x .125 102A 833148 1 Vac Mtr 240V 51 828971 1 Nut 1-1/2 Pipe Thread 103 833164 1 Pipe 1.5 x 12 (13 gal) 52 828972 1 Gasket 103A 833137 1 Pipe 1.5 x 6 (7 gal) 53 828974 1 Strainer 104 833463 1 Lead White 54 828975 2 WSR Neoprene .75 x 1.5 x .09 105 833607 1 Decal 55 808077 1 Bumper 10" *106 833826 1 Lint Bag	47	828945	1	Bulkhead Fitting 1/4 x 3/4			1	-
50 828970 3 WSR Neoprene 1.81 x 2.4 x .125 102A 833148 1 Vac Mtr 240V 51 828971 1 Nut 1-1/2 Pipe Thread 103 833164 1 Pipe 1.5 x 12 (13 gal) 52 828972 1 Gasket 103A 833137 1 Pipe 1.5 x 6 (7 gal) 53 828974 1 Strainer 104 833463 1 Lead White 54 828975 2 WSR Neoprene .75 x 1.5 x .09 105 833607 1 Decal 55 808077 1 Bumper 10" *106 833826 1 Lint Bag	48	828959	1	Plastic Elbow 1-1/2				•
51 828971 1 Nut 1-1/2 Pipe Thread 103 833164 1 Pipe 1.5 x 12 (13 gal) 52 828972 1 Gasket 103A 833137 1 Pipe 1.5 x 6 (7 gal) 53 828974 1 Strainer 104 833463 1 Lead White 54 828975 2 WSR Neoprene .75 x 1.5 x .09 105 833607 1 Decal 55 808077 1 Bumper 10" *106 833826 1 Lint Bag	49	828961	1	Cover	102	833147	1	Vac Mtr 120V
52 828972 1 Gasket 103A 833137 1 Pipe 1.5 x 6 (7 gal) 53 828974 1 Strainer 104 833463 1 Lead White 54 828975 2 WSR Neoprene .75 x 1.5 x .09 105 833607 1 Decal 55 808077 1 Bumper 10" *106 833826 1 Lint Bag	50	828970	3	WSR Neoprene 1.81 x 2.4 x .125	5 102A	833148	1	Vac Mtr 240V
52 828972 1 Gasket 103A 833137 1 Pipe 1.5 x 6 (7 gal) 53 828974 1 Strainer 104 833463 1 Lead White 54 828975 2 WSR Neoprene .75 x 1.5 x .09 105 833607 1 Decal 55 808077 1 Bumper 10" *106 833826 1 Lint Bag				•		833164	1	Pipe 1.5 x 12 (13 gal)
53 828974 1 Strainer 104 833463 1 Lead White 54 828975 2 WSR Neoprene .75 x 1.5 x .09 105 833607 1 Decal 55 808077 1 Bumper 10" *106 833826 1 Lint Bag				•	103A	833137	1	· · · · · · · · · · · · · · · · · · ·
54 828975 2 WSR Neoprene .75 x 1.5 x .09 105 833607 1 Decal 55 808077 1 Bumper 10" *106 833826 1 Lint Bag							1	
55 808077 1 Bumper 10" *106 833826 1 Lint Bag								
The state of the s				·				
	55A	828978	1	Bumper 60 1/2"				-

*Not Shown

100 PSI PUMP 833068

TROUBLE SHOOTING

Pulsating Flow - Pump Cycling On and Off

■ Restricted pump delivery. Check discharge lines, fittings, valves and spray nozzles for clogging or undersizing.

Failure to Prime — Motor Operates, But No Pump Discharge

- Restricted intake or discharge line. Open all line valves check for "jammed" check valve poppets and clean clogged lines.
- Air leak in intake line.
- Punctured pump diaphragm.
- Defective pump check valve.
- Crack in pump housing
- Worn pump bearing

Motor Fails to Turn On


- Pump or equipment not plugged in electrically.
- Loose wiring connection.
- Pressure switch failure.
- Defective motor or rectifier.

Pump Fails to Turn Off — after Discharge Valves are Closed.

- Depletion of available liquid supply.
- Punctured pump diaphragm.
- Discharge line leak.
- Defective pressure switch.
- Insufficient voltage to pump.
- Defective pump check valve.
- Worn pump bearing.

Low FLow and Pressure

- Air leak at pump intake.
- Accumulation of debris inside pump and plumbing.
- Worn pump bearing (excessive noise).
- Punctured pump diaphragm.
- Defective rectifier or motor.
- Defective pump check valve.



SERVICE TIPS

Refer to exploded view for Key Number. To disassemble, remove six pump head screws (15), rotate bearing cover (10) so drain notch is aligned with cam/bearing assembly set screw (8). Loosen set screw (use ½" size Allen Wrench) and slide pump head off shaft. Pistons (11) should always be replaced when new diaphragm is installed. Replace worn parts and reassemble. Be sure raised side of diaphragm faces the motor and radiused corner of pistons face diaphragm (coat motor shaft with grease prior to assembly). Hex stem of piston (11) must be alligned (free to enter) into hex hole in cam bearing assembly (9), otherwise diaphragm will leak. Tighten screw (7) partially, center pistons in diaphragm, then tighten screws securely.

Reassemble bearing cover and cam/bearing assembly to motor and retighten the set screw securely. Set screw MUST be positioned in shaft indentation. Positioning of this screw is critical to avoid mis-alignment and subsequent diaphragm damage.

Reassemble remaining pump head parts, using care to properly seat "O" ring (13) in check valve assembly and tighten pump head screws evenly.

PARTS LIST

ltem			
No.	Part No.	Qty.	Description
1	Not Available		
2	833654	1	Brush Endbell/Rect. Assy.
3	Not Available		
4	Not Available		
5	Not available		
6	Not available		
*7	833653	2	Cam/Bearing Screws
*8	833652	1	Cam/Bearing Set Screw
*9	833656	1	Cam/Bearing Kit
10	Not available		
*11	833657	2	Pistons
*12	833658	1	Diaphragm Kit
*13	833659	1	Check Valve
14	833661	1	Upper Housing/Switch Assy.
15	Not available		
	833660		Pump Service Kit Includes * items

TOOLS AND ACCESSORIES

829601 160 Powerhead
831255 Drag Wand Asy.
828502 Hand Extraction Tool
830750 Vac & Solution Hose 25 Ft.

LIMITED WARRANTY

Minuteman International, Inc. warrants to the original purchaser/user that this product is free from defects in workmanship and materials under normal use and service for a period of three years from date of purchase. In addition, Minuteman International, Inc. will, at its option, honor labor warranty claims for the first 12 months from date of sale, provided such claims are submitted through and approved by factory authorized repair stations. Minuteman International, Inc. will, at its option, repair or replace without charge, except for transportation costs, parts that fail under normal use and service when operated and maintained in accordance with the applicable operation and instruction manuals.

This warranty does not apply to normal wear, or to items whose life is dependent on their use and care, such as belts, cords, switches, hoses, rubber parts, electrical motor components or adjustments. Parts not manufactured by Minuteman International, Inc. such as engines, batteries, battery chargers, hydraulic pumps, and tires are covered by and subject to the warranties and/ or guarantees of their manufacturers. Please contact Minuteman International, Inc. for procedures in warranty claims against these manufacturers.

Special warning to purchaser — Use of replacement filters and/or prefilters not manufactured by Minuteman International, Inc. or its designated licensees, will void all warranties expressed or implied.

A potential health hazard exists without exact original equipment replacement.

All warranteed items become the sole property of Minuteman International, Inc. or its original manufacturer, whichever the case may be.

Minuteman International, Inc. disclaims any implied warranty, including the warranty of merchantability and the warranty of fitness for a particular purpose. Minuteman International, Inc. assumes no responsibility for any special, incidental or consequential damages.

This limited warranty is applicable only in the U.S.A. and Canada, and is extended only to the original user/purchaser of this product. Customers outside the U.S.A. and Canada should contact their local distributor for export warranty policies. Minuteman International, Inc. is not responsible for costs or repairs performed by persons other than those specifically authorized by Minuteman International, Inc. This warranty does not apply to damage from transportation, alterations by unauthorized persons, misuse or abuse of the equipment, use of non-compatible chemicals, or damage to property, or loss of income due to malfunctions of the product.

If a difficulty develops with this machine, you should contact the dealer from whom it was purchased.

This warranty gives you specific legal rights, and you may have other rights which vary from state to state. Some states do not allow the exclusion or limitation of special, incidental or consequential damages, or limitations on how long an implied warranty lasts, so the above exclusions and limitations may not apply to you.



World Headquarters
Minuteman International, Inc.
111 South Rohlwing Road
Addison, Illinois 60101

Minuteman Canada, Inc. 2210 Drew Road Mississauga, Ontario L5S 1B1

(630) 627-6900 FAX (630) 627-1130 (905) 673-3222 FAX (905) 673-5161 985721 Printed in U.S.A.